


For pricing or technical support, please email us at [sales@senko.com](mailto:sales@senko.com) or talk with your local SENKO sales representative.

PART NUMBER	IMAGE	NOTES
<b>MNT-ADP</b>		This is the inspection tip adapter you will need to hold the <b>Ø2.0mm</b> inspection tips.
<b>SMX-T-MIL-2.0-S</b>		Inspection tip for Ø2.0mm <b>MIL-DTL-29504/15</b> socket termini in MIL 28876 connectors
<b>SMX-T-MIL-2.0-P</b>		Inspection tip for Ø2.0mm <b>MIL-DTL-29504/14</b> pin termini in MIL 28876 connectors
<b>MNT-STAND</b>		<b>OPTIONAL:</b> Weighted benchtop stand for holding the MANTA+V2 scope.

### ANCILLARY SUPPORT PRODUCTS

	PART NUMBER	IMAGE	NOTES
CLEANING	<a href="#"><u>SCK-SS-M-200A</u></a>		<b>SMART CLEANER MINI 2.0MM</b> 400 cleanings 
	<a href="#"><u>AFT-G-NW</u></a>		<b>SENKO OPTICAL GRADE WIPES</b> Zip bag of 100 4X4 wipes 
	<a href="#"><u>CSK-02</u></a>		<b>2.5MM NEOCLEAN STICK</b> For MIL-DTL-29504/15 socket termini 
HANDLING	<a href="#"><u>AFT-T-TBR</u></a>		<b>SOFT STRIP THERMAL STRIPPERS</b> Precision stripping and concentric scoring of fibers 
	<a href="#"><u>AFT-G-SFP-TESTER</u></a>		<b>SFP CHECK LIGHT™ TESTER</b> SFP+ transceiver test module for live T <sub>x</sub> and R <sub>x</sub> diagnostics (No software required) 